



DA multi tool/bronze wool pad holder

Fitting Instructions

The bronze wool pad holder is already assembled and ready to use.

The DA Multi tool is packed separately. We recommend you fit this inside the adapter on the water fed pole first. Please use the 50mm bolt supplied.

The Bronze wool pad holder can then be threaded onto the DA Multi tool and is ready to use.

Some silicone grease has been applied to the threaded end of the DA Multi Tool and also to the socket on the pad holder to ensure they can be unthreaded easily.

IMPORTANT: Do not over tighten. To release - push down and turn anticlockwise.

The bronze wool pad is ideal for use on glass, UPVC, cladding, fascias, gutters and conservatory roofs.

Please note it is not recommended for use on painted surfaces, steel frames, powder coated steel frames, leaded windows, self cleaning glass or glass with a special coating or film. If using on very old UPVC it is advisable to carry out a test patch first.

Maintenance

Bronze Wool pads are non-corrosive and re-useable, they are designed to easily produce and maintain a professional looking finish. We recommend after every use the bronze wool pad is cleaned with soapy water to remove any dirt or grit so it is ready for the next job.

If you wish to replace the bronze wool pad simply undo the wing nuts to attach the new pad.